

Miniature Ethernet Acquisition Module



Applications

- CAIS applications
- Distributed systems
- Timestamping data
- Ethernet bus monitor
- Data selection from Ethernet frames
- Filter sensitive Ethernet frames from PCM outputs

Features

- Single channel 10/100BASE-T Ethernet acquisition card which interfaces with the Ethernet in a promiscuous mode
- Contains four independent filters for selecting specific Ethernet packet data from specific Ethernet frames for inclusion into the chassis' Chapter 4 PCM output
- Each filter can sort on up to three independent fields within an Ethernet frame to identify the frame for selected data
- Filters can be independently programmed to include or exclude specific Ethernet frames from the card's PCM outputs or all incoming frames can be included
- Composite data output stream Class II PCM, similar to IRIG 106 Chapter 8 - Two independently programmable on-board PCM outputs
- Receives all standard Ethernet frame up to 1522 bytes. Does not support jumbo frames or frames over 1522 bytes
- Supports ARP and PAUSE protocols
- ARP and PAUSE frames can be separately configured to be included or excluded from filter searches and the card's PCM outputs
- Multiple cards may be placed within a single chassis

Description

The ETI-201B is a member of the EDAU/PDAU/nDAU product families. The ETI-201B is a single channel Ethernet acquisition card. The card accepts all standard Ethernet packet types. It will not accept jumbo frames or any frames over 1522 Bytes. The ETI-201B has four independently programmable Ethernet frame filters. Each filter can search the incoming Ethernet frames on up to three separately programmable fields to select specific Ethernet frames for data selection. The selected data is included into the chassis's Chapter 4 PCM output. Each of the four programmable filters can store up to 256 entire selected Ethernet frames in internal frame buffers. The card has two independently programmable PCM composite output data channels that can be configured to include all incoming Ethernet traffic. The PCM outputs can also be configured to include or exclude Ethernet frames that match a specific filter's search criteria. The PCM output channels create composite output streams of Class II PCM data similar to the IRIG 106, Chapter 8 requirements. The card can buffer more than 1024 entire Ethernet frames in its internal PCM output frame buffers.

Revision 05/12/2015

ETI-201B Datasheet

©2015 Teletronics - A Curtiss-Wright Company
 Specifications subject to change without notice.
 Approved for Public Release 15-S-2631



CAIS
Compatible



Management
System
AS9100C
ISO 9001:2008

Teletronics - A Curtiss-Wright Company
 15 Terry Drive, Newtown, PA 18940
 phone: 267.352.2020 fax: 267.352.2021 Sales@ttcdas.com

www.ttcdas.com